



EXPLODED VIEW




ADJUSTMENT RANGE



144-0601 -
Wall Top Assembly:
Min: 0mm
Max: 15mm

144-0671 -
Wall Top Assembly Ext'd 15mm
Min: 15mm
Max: 30mm


1



Screw Cartridge Body into recess until Cartridge Seat meets a physical stop.


Do not over tighten.

2




Fit Fibre Washer around the Spindle and then firmly fasten the Bonnet onto the Spindle using a spanner.

3



Place the Dress Plate and Flange onto the bonnet.


5



Apply Teflon Tape to the wall thread.


Screw the Wall Outlet onto the Threaded Elbow until firmly fastened and with the spout pointed downwards.

4



Push the Handle Hub onto the Spline and tighten Screw using a screwdriver.
Screw the Handle Pin into the pinhole, and push the H&C Indicator into the front hole, ensuring it is in the correct orientation.

NOTE



• Pressure supply less than 150kPa;
NOTE: The 500kPa maximum water supply pressure does not apply to fire service outlets.

For tapware, any flow controller incorporated in the outlet to be tightened to prevent removal by hand. As Per AS3718

Failure to comply with the above may void all warranties.

WARRANTY:
Please refer to the full warranty statement enclosed with the product before installing.

MAINTENANCE AND CARE:
- Chrome plated surfaces should be cleaned with mild liquid detergent or soap and water.
- Do not use cream cleaners or citrus based cleaning products, as they are abrasive.
- Use of unsuitable cleaning agents may damage the surface. Any damage caused in this way will not be covered by warranty.

DISCLAIMER:
While we aim to ensure the specifications shown are correct at the time of printing, we reserve the right to make modifications without prior notice. Always use the physical product measurements for mark-ups and roughing-in as the line drawing shown may differ from the actual product over time.

*All measurements are shown in millimeters.



recommended working pressure

150-500KPa

maximum hot water temperature

75 degrees

